
















- i Please review all available spare parts for this item, then contact us through the webform (found in the Help Centre in our website header). Let us know the SKU of each spare part you're interested in and the quantity you need.
- i The availability of the products may change.

| Product image | SKU number | Product name | Available quantity |
|---|-----------------|---|---|
|  | 19003442 | <ul style="list-style-type: none"> i  Moduł z wyświetlaczem  Module with display  Modul mit Display SBS-LW-10 | ● 0 |
|  | 19003659 | <ul style="list-style-type: none"> i  moduł elektroniczny  elektronisches Modul  electronic modul SBS-LW-10 | ● 0 |
|  | 19003673 | <ul style="list-style-type: none"> i  PŁYTKA Z GNIAZDEM ZASILANIA  plate with the plug power  Platine mit der Versorgungssteckdose SBS-LW-10 | ● 0 |
|  | 19003821 | <ul style="list-style-type: none"> i  PŁYTKA GŁÓWNA  Hauptplatine  main board SBS-LW-10 | ● 0 |
|  | 19003822 | <ul style="list-style-type: none"> i  PŁYTKA zasilacza  PLATINE des Netzteiles  POWER SUPPLY BOARD SBS-LW-10 | ● 4 |

| Product image | SKU number | Product name | Available quantity |
|---|-----------------|---|--------------------|
|  | 19004269 | <p> Czujnik tensometryczny</p> <p> Wägezelle</p> <p> load cell SBS-LW-10</p> | ● 0 |
|  | 19006237 | <p> Naklejka SBS-LW-10</p> <p> 500</p> <p> sticker SBS-LW-10</p> | ● 9 |
|  | 19006821 | <p> Opakowanie zewnętrzne 25x24.5x7.5</p> <p> outside packaging 25x24.5x7.5</p> <p> Außenverpackung 25x24.5x7.5</p> | ● 0 |
|  | 19008205 | <p> Opakowanie zastępcze 40x40x10</p> <p> substitute packaging 40x40x10</p> | ● 0 |