

- i Please review all available spare parts for this item, then contact us through the webform (found in the Help Centre in our website header). Let us know the SKU of each spare part you're interested in and the quantity you need.
- i The availability of the products may change.

Product image	SKU number	Product name	Available quantity
	<b>19004501</b>	<ul style="list-style-type: none"> <li> KASETA DOLNA</li> <li> GÓRNA</li> <li> Kasette obere u. untere</li> </ul>	<span style="color: red;">●</span> <b>0</b>
	<b>19004538</b>	<ul style="list-style-type: none"> <li> ŻARÓWKA typ1 230V 1100W</li> <li> GLÜHBIRNE Typ 1 230V 1100W</li> <li> BULB type 1 230V 1100W IR-DRYER2000.2</li> </ul>	<span style="color: red;">●</span> <b>0</b>
	<b>19004776</b>	<ul style="list-style-type: none"> <li> KASETA ŚRODKOWA</li> <li> mittlere KASSETTE</li> <li> central BOX IR-DRYER3000.2</li> </ul>	<span style="color: red;">●</span> <b>0</b>
	<b>19004846</b>	<ul style="list-style-type: none"> <li> SIŁOWNIK</li> <li> gas lifter IR-DRYER3000.1</li> </ul>	<span style="color: green;">●</span> <b>1</b>
	<b>19005719</b>	<ul style="list-style-type: none"> <li> ŻARÓWKA typ2 230V 1100W</li> <li> GLÜHBIRNE Typ2 230V 1100W</li> <li> BULB type2 230V 1100W</li> </ul>	<span style="color: red;">●</span> <b>0</b>

Product image	SKU number	Product name	Available quantity
	<b>19006561</b>	<p>🇵🇱 Opakowanie zewnętrzne 25x73,5x84 box1</p> <p>🇬🇧 outside packaging 25x73,5x84 box1</p> <p>🇩🇪 Außenverpackung 25x73,5x84 box1</p>	● <b>3</b>
	<b>19006562</b>	<p>🇵🇱 Opakowanie zewnętrzne 16x163x75 box2</p> <p>🇬🇧 outside packaging 16x163x75 box2</p> <p>🇩🇪 Außenverpackung 16x163x75 box2</p>	● <b>2</b>
	<b>19006563</b>	<p>🇵🇱 Opakowanie zewnętrzne 9x99x110 box3</p> <p>🇬🇧 outside packaging 9x99x110 box3</p> <p>🇩🇪 Außenverpackung 9x99x110 box3</p>	● <b>6</b>
	<b>19006621</b>	<p>🇵🇱 Tyrystor MTX 110-12</p> <p>🇬🇧 Thyristor MTX 110-12</p>	● <b>1</b>
	<b>19006622</b>	<p>🇵🇱 Transformator</p> <p>🇬🇧 Transformer</p>	● <b>3</b>
	<b>19008525</b>	<p>🇵🇱 Słup-maszt z modułem sterującym</p> <p>🇬🇧 Pole-mast with control module</p>	● <b>0</b>

Product image	SKU number	Product name	Available quantity
	<b>19009160</b>	<ul style="list-style-type: none"> <li> Płyta ze sterownikiem mikroprocesorowym FY-KD3W-TP01</li> <li> A board with a microprocessor controller FY-KD3W-TP01</li> </ul>	<ul style="list-style-type: none"> <li><span style="color: red;">●</span> <b>0</b></li> </ul>
	<b>19009910</b>	<ul style="list-style-type: none"> <li> Łącznik metalowy z gwintem fi 12</li> <li> Metal connector with di 12 thread</li> </ul>	<ul style="list-style-type: none"> <li><span style="color: green;">●</span> <b>5</b></li> </ul>
	<b>19009911</b>	<ul style="list-style-type: none"> <li> Nakrętka samokontruująca fi12</li> <li> Self-locking nut di 12</li> </ul>	<ul style="list-style-type: none"> <li><span style="color: red;">●</span> <b>0</b></li> </ul>
	<b>19009912</b>	<ul style="list-style-type: none"> <li> Podkładka metalowa fi 12.1</li> <li> Metal washer di 12.1</li> </ul>	<ul style="list-style-type: none"> <li><span style="color: red;">●</span> <b>0</b></li> </ul>
	<b>19009977</b>	<ul style="list-style-type: none"> <li> Osłona plastikowa</li> <li> Plastic top cover</li> </ul>	<ul style="list-style-type: none"> <li><span style="color: green;">●</span> <b>4</b></li> </ul>
	<b>19010388</b>	<ul style="list-style-type: none"> <li> Uchwyt metalowy czarny</li> <li> U-bracket</li> </ul>	<ul style="list-style-type: none"> <li><span style="color: red;">●</span> <b>0</b></li> </ul>

Product image	SKU number	Product name	Available quantity
	<b>19010389</b>	<p>🇵🇱 Uchwyt metalowy żółty</p> <p>🇬🇧 Yellow metal handle</p>	● 11
	<b>19014303</b>	<p>🇵🇱 BOX 2 kompletny</p> <p>🇬🇧 BOX 2 complete</p>	● 1
	<b>19022865</b>	<p>🇵🇱 BOX 3 Kompletny</p> <p>🇬🇧 BOX 3 Complete</p>	● 0
	<b>19027248</b>	<p>🇵🇱 Wyłącznik bezpieczeństwa</p> <p>🇬🇧 Safety switch</p>	● 1